


## Product data sheet

### Characteristics

# A9N21038

Comb Busbar, Acti9, 3L+N balanced with Aux and Vigi - 9 mm pitch - 56 modules



### Main

Range	Acti9
Product or component type	Comb busbar
Mounting mode	Horizontal
Accessory / separate part category	Connection accessory
Lines description	3L + N
Length in 18 mm modules	56

### Complementary

Number of ways	22 ways Aux + N + L + Vigi
Poles configuration for 1 way	1 x 1P + N
Connection pitch	9 mm between phase and neutral
Connector type	Tooth
Distance between way	45 mm
Marking	N L1 N L2 N L3
Insulation	Insulated
Device presentation	Cuttable
[Ie] rated operational current	63 A at 40 °C
[Ue] rated operational voltage	230 V AC Ph/N
[Ui] rated insulation voltage	500 V AC conforming to IEC 61439-2
Mounting location	Top on tunnel type terminals
9 mm pitches	112
Width	1000 mm
Colour	Light grey (RAL 7035)
Range compatibility	Acti9 Acti9 C40 Acti9 Acti9 DT40 Acti9 Acti9 DT40 Vigi Acti9 Acti9 iDPN Acti9 Acti9 DT60 Acti9 Acti9 DPN Vigi Multi9 Multi9 N40 Vigi

### Environment

Standards	EN/IEC 61439-1
Fire resistance	960 °C ( 30 s ) conforming to IEC 60695-2-1
Pollution degree	3 conforming to IEC 60947-7-1
IP degree of protection	IP20 with end-pieces and tooth covers

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	5.000 cm
Package 1 Length	97.000 cm
Package 1 Weight	772.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	8.500 cm
Package 2 Width	107.000 cm
Package 2 Length	10.000 cm
Package 2 Weight	4.175 kg
Unit Type of Package 3	P12
Number of Units in Package 3	200
Package 3 Height	75.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	179.000 kg

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------