

Product data sheet

Characteristics

A9N26917

Auxiliary contact, Acti9, SD, 1 C/O, 2mA to 100mA, 24VAC to 250VAC, 24VDC to 220VDC, bottom connection



Main

Range of product	Acti9
Product or component type	Fault contact
Device short name	SD
Signal contacts composition	1 C/O
[In] rated current	2...100 MA at 24...240 V, AC 50/60 Hz 2...100 MA at 24 V, DC 2...100 MA at 48 V, DC 2...100 MA at 60 V, DC 2...100 MA at 130 V, DC 2...100 mA at 220 V, DC
9 mm pitches	1

Complementary

Operating mode	Daisy chain up to 100 devices
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	4 kV
Local signalling	Mechanical indicator
Mounting mode	Clip-on
Mounting location	Left side of circuit-breaker
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Top: YES
Height	85.3 mm
Width	9 mm
Depth	68 mm
Product weight	30 g
Colour	White
Connections - terminals	Screw clamp terminal (bottom) 1 cable(s) 0.5...2.5 mm ² - rigid Screw clamp terminal (bottom) 2 cable(s) 1.5 mm ² - flexible Screw clamp terminal (bottom) 2 cable(s) 1.5 mm ² - flexible with ferrule
Wire stripping length	9 mm
Tightening torque	1 N.m bottom

Environment

Standards	EN/IEC 60947-5-1 EN/IEC 60947-5-4 GB/T 14048.5 GB/T 14048.17
Product certifications	CE[RETURN]UKCA
Quality labels	EAC CCC
IP degree of protection	IP20
Pollution degree	3
Tropicalisation	2

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.000 cm
Package 1 Width	1.800 cm
Package 1 Length	7.500 cm
Package 1 Weight	38.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	23.400 cm
Package 2 Width	10.000 cm
Package 2 Length	8.700 cm
Package 2 Weight	522.000 g
Unit Type of Package 3	S03
Number of Units in Package 3	120
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	6.000 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations