

Product data sheet

Characteristics

A9N26929

Acti9 - Auxiliary contact OC plus 1 SD and OF ac dc



Main

Range of product	Clario Acti 9 Prodis Librio
Product or component type	Double OC or fault contact
Device short name	OF and OF or OF and SD
Signal contacts composition	2 C/O
[In] rated current	1 A: 130 V DC 2 A: 48 V DC 6 A: 24 V DC 3 A: 415 V AC - 50/60 Hz 6 A: 240 V AC - 50/60 Hz
9 mm pitches	1

Complementary

Range compatibility	Acti9 DPN Vigi Acti9 RCCB-ID Acti9 iDPN Vigi Acti9 C60H-DC Acti 9 C60PV-DC Acti 9 C40 Acti9 ID C40 Acti 9 C120 Acti 9 DT40 Acti 9 DT60 Acti9 IDc Acti 9 C120NA-DC Acti 9 iDPN Acti9 ITG40 Acti 9 SW60-DC Acti 9 C60NA-DC Acti 9 C40 Vigi Acti 9 DT40 Vigi
Mounting mode	Fixed
Mounting support	DIN rail
Comb busbar and distribution block compatibility	NO
Height	90 mm
Width	9 mm
Depth	73.5 mm
Net weight	38 g
Colour	White
Connections - terminals	Screw clamp terminal (top and bottom) 2 cable(s) 1.5 mm ² - flexible Screw clamp terminal (top and bottom) 1 cable(s) 0.5...2.5 mm ² - rigid Screw clamp terminal (top and bottom) 2 cable(s) 1.5 mm ² - flexible with ferrule
Wire stripping length	9 mm
Tightening torque	1 N.m

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Standards	EN/IEC 60947-5-1
Product certifications	ASTA ASEFA LCIE KEMA
IP degree of protection	IP20 conforming to EN/IEC 60947-5-1
Pollution degree	3 conforming to EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	46.0 g
Package 1 Height	2.2 cm
Package 1 width	8.0 cm
Package 1 Length	9.2 cm
Unit Type of Package 2	S03
Number of Units in Package 2	108
Package 2 Weight	5.94 kg
Package 2 Height	30.0 cm
Package 2 width	30.0 cm
Package 2 Length	40.0 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	12
Package 3 Weight	606.0 g
Package 3 Height	8.7 cm
Package 3 width	10.0 cm
Package 3 Length	26.5 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------