

## Product data sheet

### Characteristics

# A9N26960

## Voltage release MN 220-240Vac dc



### Main

Range of product	Clario Prodis Librio Acti 9
Product or component type	Undervoltage release
Device short name	MN
[Uc] control circuit voltage	220...240 V AC 50/60 Hz
Control type	Standard
9 mm pitches	2

### Complementary

Range compatibility	Acti 9 iDPN Acti 9 C120 Acti 9 C40 Acti 9 C60H-DC Acti 9 C60NA-DC Acti 9 C60PV-DC Acti 9 DPN Vigi Acti 9 DT40 Acti 9 DT60 Acti 9 ID C40 Acti 9 IDc Acti 9 ITG40 Acti 9 ID Acti 9 DPN
Local signalling	Action indicator
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
Height	82.5 mm
Width	18 mm
Depth	73.5 mm
Net weight	66 g
Colour	White
Connections - terminals	Clamp terminal - 1 cable(s) 2.5 mm <sup>2</sup> - flexible Clamp terminal - 1 cable(s) 2.5 mm <sup>2</sup> - rigid Clamp terminal - 2 cable(s) 1.5 mm <sup>2</sup> - flexible Clamp terminal - 2 cable(s) 1.5 mm <sup>2</sup> - rigid
Wire stripping length	9 mm
Tightening torque	1 N.m
Compatibility code	MN

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

Standards	EN/IEC 60947-5-1
Product certifications	KEMA ASTA LCIE ASEFA
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...85 °C

## Packing Units

Package 1 Weight	0.079 kg
Package 1 Height	0.280 dm
Package 1 width	0.800 dm
Package 1 Length	0.940 dm

## Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------