

## Product data sheet

### Characteristics

# A9N26963

## Voltage release, Acti9, MN (S) 220-240VAC DC



### Main

Range of product	Acti9
Product or component type	Undervoltage release
Device short name	MNs
[Uc] control circuit voltage	220...240 V AC 50/60 Hz
Control type	Delayed
9 mm pitches	2

### Complementary

Range compatibility	Acti9 iDPN Acti9 C120 Acti9 C40 Acti9 C60H-DC Acti9 C60NA-DC Acti9 C60PV-DC Acti9 DPN Vigi Acti9 DT40 Acti9 DT60 Acti9 ID C40 Acti9 IDc Acti9 ITG40 Acti9 ID Acti9 DPN
Local signalling	Action indicator
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
Comb busbar and distribution block compatibility	Top: YES
Height	82.5 mm
Width	18 mm
Depth	73.5 mm
Net weight	66 g
Colour	White
Connections - terminals	Screw clamp terminal (bottom) - 2 cable(s) 1.5 mm <sup>2</sup> - flexible Screw clamp terminal (bottom) - 2 cable(s) 1.5 mm <sup>2</sup> - flexible with ferrule Screw clamp terminal (bottom) - 1 cable(s) 0.5...2.5 mm <sup>2</sup> - rigid
Wire stripping length	9 mm for bottom connection
Tightening torque	1 N.m bottom
Compatibility code	MNs

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

Standards	EN/IEC 60947-1
Product certifications	LCIE[RETURN]ASTA[RETURN]KEMA[RETURN]ASEFA
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...85 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.900 cm
Package 1 Width	8.000 cm
Package 1 Length	9.400 cm
Package 1 Weight	76.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	9.000 cm
Package 2 Width	10.000 cm
Package 2 Length	26.700 cm
Package 2 Weight	662.000 g
Unit Type of Package 3	S03
Number of Units in Package 3	72
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	6.442 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------