

Product data sheet

Characteristics

ABC15DMLBLF-WE

SWITCHED SOCKET MECHANISM DOUBLE POLE SINGLE



Main

Range of product	Series ABC
Product brand	Clipsal
Colour	White electric

Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Switch Rocker
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Stainless steel
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	70 mm
Length	220 mm
Width	175 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	58.0 g
Package 1 Height	7 cm
Package 1 width	17.5 cm
Package 1 Length	22 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	580.0 g
Package 2 Height	7.2 cm

Package 2 width	11.7 cm
Package 2 Length	15.4 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Weight	5800.0 g
Package 3 Height	22.6 cm
Package 3 width	19.1 cm
Package 3 Length	35.9 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile