

## Product data sheet

### Characteristics

# ABC15VDNMLBF-WE

## Metal Plate Series, Switched Socket Mechanism Double Pole Single



### Main

Range of product	Series ABC
Product or component type	Switched socket
Product brand	Clipsal

### Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Switch Rocker
Fixing mode	By screws
Local signalling	Indicator light
Mounting position	Vertical
Material	Stainless steel
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	70 mm
Length	220 mm
Width	175 mm

### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7 cm
Package 1 Width	17.5 cm
Package 1 Length	22 cm
Package 1 Weight	0.072 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	117 cm
Package 2 Width	143 cm

Package 2 Length	181 cm
Package 2 Weight	0.72 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	254 cm
Package 3 Width	348 cm
Package 3 Length	445 cm
Package 3 Weight	7.2 kg