

Product data sheet

Characteristics

ACTFM1UF2LC12PM

Actassi Fibre Optic Front Adapters Plate with 12 x LC Dplx MM Adapters



Main

Range	Actassi
Product	Cover plate with adapters
Product destination	Fibre optic panel
Provided equipment	12 duplex multi-mode adaptor for LC

Complementary

Material	PC
Fixing mode	Snap-in
Colour	Black
Width	120 mm
Height	35 mm
Depth	5.6 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	60.4 g
Package 1 Height	4.7 cm
Package 1 width	4.7 cm
Package 1 Length	14 cm
Unit Type of Package 2	P12
Number of Units in Package 2	2304
Package 2 Weight	168.462 kg
Package 2 Height	102 cm
Package 2 width	80 cm
Package 2 Length	120 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	96
Package 3 Weight	6.498 kg
Package 3 Height	30 cm
Package 3 width	29.9 cm
Package 3 Length	39.8 cm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile