

Product data sheet

Characteristics

ACTMP1U

Actassi, Panel 19INC 1U Unloaded Max 3 Plates



Main

Range of product	Actassi
Product or component type	Fibre patch panel
Device presentation	Empty

Complementary

Product compatibility	3 optic cassette 3 adaptor plate
Number of optic fibre	72
Integrated connection type	LC
Number of port	72
Number of rack unit	1U
Height	44 mm
Width	482 mm
Depth	300 mm
Targeted region	Asia Pacific. Europe

Environment

Standards	EIA-310D TIA/EIA-568
-----------	-------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.42 cm
Package 1 Width	48.0 cm
Package 1 Length	40.0 cm
Package 1 Weight	5.6 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	12
Package 2 Height	87.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	80.3 kg

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes