

Product data sheet

Characteristics

ACTMP4U

PANEL 19INC 4U UNLOADED MAX 12 PLATES



Main

| | |
|---------------------------|-------------------|
| Range of product | Actassi |
| Product or component type | Fibre patch panel |
| Device presentation | Empty |

Complementary

| | |
|----------------------------|---------------------------------------|
| Product compatibility | 12 optic cassette 12 adaptor plate |
| Number of optic fibre | 288 |
| Integrated connection type | LC |
| Number of port | 288 |
| Number of rack unit | 4U |
| Height | 175 mm |
| Width | 482 mm |
| Depth | 300 mm |
| Targeted region | Asia Pacific. Europe |

Environment

| | |
|-----------|-------------------------|
| Standards | EIA-310D TIA/EIA-568 |
|-----------|-------------------------|

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 10.6 kg |
| Package 1 Height | 25 cm |
| Package 1 width | 48.5 cm |
| Package 1 Length | 57.5 cm |
| Unit Type of Package 2 | P12 |
| Number of Units in Package 2 | 6 |
| Package 2 Weight | 76.1 kg |
| Package 2 Height | 87 cm |
| Package 2 width | 80 cm |
| Package 2 Length | 120 cm |

Offer Sustainability

| | |
|----------------------------|--|
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |