

Product data sheet

Characteristics

ACTMP4U

Panel 19INC 4U Unloaded Max 12 Plates, Actassi

Main

Range of product	Actassi
Product or component type	Fibre patch panel
Device presentation	Empty

Complementary

Product compatibility	12 optic cassette 12 adaptor plate
Number of optic fibre	288
Integrated connection type	LC
Number of port	288
Number of rack unit	4U
Height	175 mm
Width	482 mm
Depth	300 mm
Targeted region	Asia Pacific. Europe

Environment

Standards	EIA-310D TIA/EIA-568
-----------	-------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	27.000 cm
Package 1 Width	49.000 cm
Package 1 Length	58.000 cm
Package 1 Weight	10.666 kg
Unit Type of Package 2	P12
Number of Units in Package 2	8
Package 2 Height	93.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	96.328 kg

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Circularity Profile	No need of specific recycling operations