

## Product data sheet

### Characteristics

# AK2CA6

## Cover, Spacial CRN, for Cable Clip



### Main

Product or component type	Cover
Accessory / separate part categor	Cabling accessories
Range compatibility	PanelSeT S3D PanelSeT CRN Thalassa PLA Thalassa PLS Thalassa PLM
Mounting support	Cable duct width= 60 mm
Quantity per set	Set of 8

### Complementary

Colour	Blue (RAL 5000)
Length	2000 mm
Width	60 mm
Material	PVC (polyvinyl chloride)
Net weight	0.43 kg

### Environment

Ambient air temperature for operation	-5...60 °C
Flame retardance	V-0 conforming to UL 94
Fire resistance	960 °C conforming to IEC 60695-2-1/1
Standards	VDE 0506 DIN 43659 VDE 0660

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.0 cm
Package 1 Width	10.0 cm
Package 1 Length	200.0 cm
Package 1 Weight	457.0 g
Unit Type of Package 2	PAL
Number of Units in Package 2	1120
Package 2 Height	108.0 cm
Package 2 Width	201.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	597.0 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	8
Package 3 Height	201.0 cm
Package 3 Width	11.5 cm
Package 3 Length	6.5 cm
Package 3 Weight	4.04 kg

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------