


Product data sheet

Characteristics

AK2CA6

Cover for cable duct - Width=60mm



Main

Product or component type	Cover
Accessory / separate part category	Cabling accessories
Range compatibility	S3D CRN PLA PLS PLM
Mounting support	Cable duct width= 60 mm
Quantity per set	Set of 8

Complementary

Colour	Blue (RAL 5000)
Length	2000 mm
Width	60 mm
Material	PVC (polyvinyl chloride)
Net weight	0.43 kg

Environment

Ambient air temperature for operation	-5...60 °C
Flame retardance	V-0 conforming to UL 94
Fire resistance	960 °C conforming to IEC 60695-2-1/1
Standards	VDE 0506 DIN 43659 VDE 0660

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	454.0 g
Package 1 Height	6 cm
Package 1 width	10 cm
Package 1 Length	200 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Weight	3.64 kg
Package 2 Height	6 cm
Package 2 width	10 cm
Package 2 Length	200 cm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------