

## Product data sheet

### Characteristics

# AK2CD100

## Spacial CRN, Cover for Cable Duct DIN



### Main

Product or component type	Cover
Accessory / separate part categor	Cabling accessories
Range compatibility	PanelSeT S3D PanelSeT CRN Thalassa PLA Thalassa PLS Thalassa PLM
Mounting support	Cable duct width= 100 mm
Quantity per set	Set of 8

### Complementary

Colour	Grey (RAL 7030)
Length	2000 mm
Width	100 mm
Material	PVC (polyvinyl chloride)
Net weight	0.48 kg

### Environment

Ambient air temperature for operation	-5...60 °C
Flame retardance	V-0 conforming to UL 94
Fire resistance	960 °C conforming to IEC 60695-2-1/1
Standards	DIN 43659 VDE 0506 VDE 0660

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.000 cm
Package 1 Width	10.000 cm
Package 1 Length	200.000 cm
Package 1 Weight	703.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	3.500 cm
Package 2 Width	10.000 cm
Package 2 Length	200.000 cm
Package 2 Weight	5.739 kg
Unit Type of Package 3	P2M
Number of Units in Package 3	320
Package 3 Height	45.000 cm
Package 3 Width	200.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	239.960 kg

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------