

## Product data sheet

### Characteristics

# AK2CD125

## Cover, Spacial CRN, for Cable Duct DIN

### Main

Product or component type	Cover
Accessory / separate part category	Cabling accessories
Range compatibility	PanelSeT S3D PanelSeT CRN Thalassa PLA Thalassa PLS Thalassa PLM
Mounting support	Cable duct width= 125 mm
Quantity per set	Set of 8

### Complementary

Colour	Grey (RAL 7030)
Length	2000 mm
Width	125 mm
Material	PVC (polyvinyl chloride)
Net weight	0.6 kg

### Environment

Ambient air temperature for operation	-5...60 °C
Flame retardance	V-0 conforming to UL 94
Fire resistance	960 °C conforming to IEC 60695-2-1/1
Standards	VDE 0506 VDE 0660 DIN 43659

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.000 cm
Package 1 Width	12.500 cm
Package 1 Length	200.000 cm
Package 1 Weight	605.000 g
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	3.500 cm
Package 2 Width	12.500 cm
Package 2 Length	200.500 cm
Package 2 Weight	4.840 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	96
Package 3 Height	24.000 cm
Package 3 Width	120.000 cm
Package 3 Length	200.500 cm
Package 3 Weight	90.000 kg

## Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Take-back	No

## Contractual warranty

Warranty	18 months
----------	-----------