

Product data sheet

Characteristics

AK2CD25

Spacial CRN, Cover for Cable Duct DIN



Main

Product or component type	Cover
Accessory / separate part category	Cabling accessories
Range compatibility	Spacial (S3D) Spacial (CRN) Thalassa PLA Thalassa PLS Thalassa PLM
Mounting support	Cable duct width= 25 mm
Quantity per set	Set of 8

Complementary

Colour	Grey (RAL 7030)
Length	2000 mm
Width	25 mm
Material	PVC (polyvinyl chloride)
Net weight	0.16 kg

Environment

Ambient air temperature for operation	-5...60 °C
Flame retardance	V-0 conforming to UL 94
Fire resistance	960 °C conforming to IEC 60695-2-1/1
Standards	DIN 43659 VDE 0506 VDE 0660

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.000 cm
Package 1 Width	2.500 cm
Package 1 Length	200.500 cm
Package 1 Weight	157.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	3.000 cm
Package 2 Width	4.000 cm
Package 2 Length	202.000 cm
Package 2 Weight	1.544 kg

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------