

## Product data sheet

### Characteristics

# AK2CD75

## Cover, Spacial CRN, for Cable Duct DIN

### Main

Product or component type	Cover
Accessory / separate part category	Cablings accessories
Range compatibility	PanelSeT S3D PanelSeT CRN Thalassa PLA Thalassa PLS Thalassa PLM
Mounting support	Cable duct width= 75 mm
Quantity per set	Set of 8

### Complementary

Colour	Grey (RAL 7030)
Length	2000 mm
Width	75 mm
Material	PVC (polyvinyl chloride)
Net weight	0.38 kg

### Environment

Ambient air temperature for operation	-5...60 °C
Flame retardance	V-0 conforming to UL 94
Fire resistance	960 °C conforming to IEC 60695-2-1/1
Standards	VDE 0660 VDE 0506 DIN 43659

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.000 cm
Package 1 Width	7.500 cm
Package 1 Length	200.000 cm
Package 1 Weight	401.000 g
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	4.500 cm
Package 2 Width	7.500 cm
Package 2 Length	201.000 cm
Package 2 Weight	3.208 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	960
Package 3 Height	45.000 cm
Package 3 Width	120.000 cm
Package 3 Length	201.000 cm
Package 3 Weight	416.960 kg

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------