

## Product data sheet

### Characteristics

# AK2GA35

Spacial CRN, Cable duct, 55 x 30 mm, without cover, blue



### Main

Product or component type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	Spacial (S3D) Spacial (CRN) Thalassa PLA Thalassa PLS Thalassa PLM
Device composition	Without cover
Quantity per set	Set of 8

### Complementary

Colour	Blue (RAL 5000)
Fixing mode	Clip-on support By screws
Material	PVC (polyvinyl chloride)
Height	55 mm
Length	2000 mm
Width	30 mm
Net weight	0.8 kg
Total number of wires	110

### Environment

Ambient air temperature for operation	-5...60 °C
Flame retardance	V-0 conforming to UL 94
Fire resistance	960 °C conforming to IEC 60695-2-1/1
Standards	DIN 43659 VDE 0506 VDE 0660 NF C 68-102

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	11.0 cm
Package 1 Length	200.0 cm
Package 1 Weight	625.0 g
Unit Type of Package 2	PAL
Number of Units in Package 2	320
Package 2 Height	77.0 cm
Package 2 Width	280.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	200.0 kg
Unit Type of Package 3	CAR

Number of Units in Package 3	8
Package 3 Height	11.0 cm
Package 3 Width	85.0 cm
Package 3 Length	200.0 cm
Package 3 Weight	5.0 kg

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

### Contractual warranty

Warranty	18 months
----------	-----------