


Product data sheet

Characteristics

AK2GA35

Cable duct - 55 x 30 mm - without cover - blue



Main

Product or component type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	S3D CRN PLA PLS PLM
Device composition	Without cover
Quantity per set	Set of 8

Complementary

Colour	Blue (RAL 5000)
Fixing mode	Clip-on support By screws
Material	PVC (polyvinyl chloride)
Height	55 mm
Length	2000 mm
Width	30 mm
Net weight	0.8 kg
Total number of wires	110

Environment

Ambient air temperature for operation	-5...60 °C
Flame retardance	V-0 conforming to UL 94
Fire resistance	960 °C conforming to IEC 60695-2-1/1
Standards	DIN 43659 VDE 0506 VDE 0660 NF C 68-102

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	625 g
Package 1 Height	8.5 cm
Package 1 width	11 cm
Package 1 Length	200 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Weight	5 kg
Package 2 Height	11 cm
Package 2 width	85 cm
Package 2 Length	200 cm
Unit Type of Package 3	PAL

Number of Units in Package 3	320
Package 3 Weight	200 kg
Package 3 Height	77 cm
Package 3 width	280 cm
Package 3 Length	120 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------