

Product data sheet

Characteristics

AK2GA39

Cable duct, Spacial CRN, 90 x 30 mm, without cover, blue

Main

Product or component type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	PanelSeT S3D PanelSeT CRN Thalassa PLA Thalassa PLS Thalassa PLM
Device composition	Without cover
Quantity per set	Set of 8

Complementary

Colour	Blue (RAL 5000)
Fixing mode	By screws Clip-on support
Material	PVC (polyvinyl chloride)
Height	90 mm
Length	2000 mm
Width	30 mm
Net weight	1.12 kg
Total number of wires	200

Environment

Ambient air temperature for operation	-5...60 °C
Flame retardance	V-0 conforming to UL 94
Fire resistance	960 °C conforming to IEC 60695-2-1/1
Standards	VDE 0506 DIN 43659 NF C 68-102 VDE 0660

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.500 cm
Package 1 Width	18.500 cm
Package 1 Length	200.000 cm
Package 1 Weight	792.000 g
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	8.000 cm
Package 2 Width	18.500 cm
Package 2 Length	201.000 cm
Package 2 Weight	6.336 kg
Unit Type of Package 3	PAL

Number of Units in Package 3	336
Package 3 Height	70.000 cm
Package 3 Width	120.000 cm
Package 3 Length	202.000 cm
Package 3 Weight	296.200 kg

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Take-back	No

Contractual warranty

Warranty	18 months
----------	-----------