


Product data sheet

Characteristics

AK2GA39

Cable duct - 90 x 30 mm - without cover - blue



Main

Product or component type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	S3D CRN PLA PLS PLM
Device composition	Without cover
Quantity per set	Set of 8

Complementary

Colour	Blue (RAL 5000)
Fixing mode	By screws Clip-on support
Material	PVC (polyvinyl chloride)
Height	90 mm
Length	2000 mm
Width	30 mm
Net weight	1.12 kg
Total number of wires	200



Environment

Ambient air temperature for operation	-5...60 °C
Flame retardance	V-0 conforming to UL 94
Fire resistance	960 °C conforming to IEC 60695-2-1/1
Standards	VDE 0506 DIN 43659 NF C 68-102 VDE 0660

Packing Units

Package 1 Weight	1.675 kg
Package 1 Height	1.850 dm
Package 1 width	0.850 dm
Package 1 Length	20.000 dm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------