

Product data sheet

Characteristics

AK2GA39

Spacial CRN, Cable duct, 90 x 30 mm, without cover, blue



Main

Product or component type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	Spacial (S3D) Spacial (CRN) Thalassa PLA Thalassa PLS Thalassa PLM
Device composition	Without cover
Quantity per set	Set of 8

Complementary

Colour	Blue (RAL 5000)
Fixing mode	By screws Clip-on support
Material	PVC (polyvinyl chloride)
Height	90 mm
Length	2000 mm
Width	30 mm
Net weight	1.12 kg
Total number of wires	200

Environment

Ambient air temperature for operation	-5...60 °C
Flame retardance	V-0 conforming to UL 94
Fire resistance	960 °C conforming to IEC 60695-2-1/1
Standards	VDE 0506 DIN 43659 NF C 68-102 VDE 0660

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	18.5 cm
Package 1 Width	8.5 cm
Package 1 Length	200.0 cm
Package 1 Weight	1.675 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	240
Package 2 Height	77.0 cm
Package 2 Width	280.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	410.0 kg
Unit Type of Package 3	CAR

Number of Units in Package 3	8
Package 3 Height	8.5 cm
Package 3 Width	18.5 cm
Package 3 Length	200.0 cm
Package 3 Weight	13.4 kg

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------