


Product data sheet

Characteristics

AK2GA69

Cable duct - 90 x 60 mm - without cover - blue



Main

Product or component type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	Spacial (S3D) Spacial (CRN) Thalassa PLA Thalassa PLS Thalassa PLM
Device composition	Without cover
Quantity per set	Set of 8

Complementary

Colour	Blue (RAL 5000)
Fixing mode	Clip-on support By screws
Material	PVC (polyvinyl chloride)
Height	90 mm
Length	2000 mm
Width	60 mm
Net weight	1.2 kg
Total number of wires	400

Environment

Ambient air temperature for operation	-5...60 °C
Flame retardance	V-0 conforming to UL 94
Fire resistance	960 °C conforming to IEC 60695-2-1/1
Standards	NF C 68-102 VDE 0506 VDE 0660 DIN 43659

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	18.5 cm
Package 1 Width	14.5 cm
Package 1 Length	215 cm
Package 1 Weight	916 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	18.5 cm
Package 2 Width	14.5 cm
Package 2 Length	200 cm
Package 2 Weight	8 kg
Unit Type of Package 3	PAL

Number of Units in Package 3	288
Package 3 Height	215 cm
Package 3 Width	140 cm
Package 3 Length	90 cm
Package 3 Weight	536 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------