


Product data sheet

Characteristics

AK2GD12575

Cable duct - 75 x 125 mm - without cover - grey



Main

Product or component type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	S3D CRN PLA PLS PLM
Device composition	Without cover
Quantity per set	Set of 8




Complementary

Colour	Grey (RAL 7030)
Fixing mode	By screws Clip-on support
Material	PVC (polyvinyl chloride)
Height	75 mm
Length	2000 mm
Width	125 mm
Net weight	1.36 kg
Total number of wires	700

Environment

Ambient air temperature for operation	-5...60 °C
Flame retardance	V-0 conforming to UL 94
Fire resistance	960 °C conforming to IEC 60695-2-1/1
Standards	VDE 0660 VDE 0506 DIN 43659

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty

18 months
