


Product data sheet

Characteristics

AK2GD2550

Spacial CRN, Cable duct, 50 x 25 mm, without cover, grey



Main

Product or component type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	Spacial S3D Spacial CRN Thalassa PLA Thalassa PLS Thalassa PLM
Device composition	Without cover
Quantity per set	Set of 8

Complementary

Colour	Grey (RAL 7030)
Fixing mode	By screws Clip-on support
Material	PVC (polyvinyl chloride)
Height	50 mm
Length	2000 mm
Width	25 mm
Net weight	0.46 kg
Total number of wires	65

Environment

Ambient air temperature for operation	-5...60 °C
Flame retardance	V-0 conforming to UL 94
Fire resistance	960 °C conforming to IEC 60695-2-1/1
Standards	DIN 43659 VDE 0506 VDE 0660

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.0 cm
Package 1 Width	6.0 cm
Package 1 Length	200.0 cm
Package 1 Weight	425.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	6.0 cm
Package 2 Width	10.0 cm
Package 2 Length	200.0 cm
Package 2 Weight	3.4 kg
Unit Type of Package 3	P2M

Number of Units in Package 3	760
Package 3 Height	120 cm
Package 3 Width	201 cm
Package 3 Length	60 cm
Package 3 Weight	320 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------