


Product data sheet

Characteristics

AK2GD3775

Spacial CRN, Cable duct, 75 x 37.5 mm, without cover, grey



Main

Product or component type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	Spacial (S3D) Spacial (CRN) Thalassa PLA Thalassa PLS Thalassa PLM
Device composition	Without cover
Quantity per set	Set of 8

Complementary

Colour	Grey (RAL 7030)
Fixing mode	Clip-on support By screws
Material	PVC (polyvinyl chloride)
Height	75 mm
Length	2000 mm
Width	37.5 mm
Net weight	0.8 kg
Total number of wires	160

Environment

Ambient air temperature for operation	-5...60 °C
Flame retardance	V-0 conforming to UL 94
Fire resistance	960 °C conforming to IEC 60695-2-1/1
Standards	VDE 0660 VDE 0506 DIN 43659

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.500 cm
Package 1 Width	7.000 cm
Package 1 Length	200.000 cm
Package 1 Weight	1.123 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	8.000 cm
Package 2 Width	14.500 cm
Package 2 Length	200.000 cm
Package 2 Weight	9.271 kg

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------