


Product data sheet

Characteristics

AK2GD5075

Spacial CRN, Cable duct, 75 x 50 mm, without cover, grey



Main

| | |
|------------------------------------|----------------------------------------------------------------------------|
| Product or component type | Cable duct |
| Accessory / separate part category | Cabling accessories |
| Range compatibility | Spacial S3D Spacial CRN Thalassa PLA Thalassa PLS Thalassa PLM |
| Device composition | Without cover |
| Quantity per set | Set of 8 |

Complementary

| | |
|-----------------------|------------------------------|
| Colour | Grey (RAL 7030) |
| Fixing mode | By screws Clip-on support |
| Material | PVC (polyvinyl chloride) |
| Height | 75 mm |
| Length | 2000 mm |
| Width | 50 mm |
| Net weight | 0.88 kg |
| Total number of wires | 240 |

Environment

| | |
|---------------------------------------|--------------------------------------|
| Ambient air temperature for operation | -5...60 °C |
| Flame retardance | V-0 conforming to UL 94 |
| Fire resistance | 960 °C conforming to IEC 60695-2-1/1 |
| Standards | DIN 43659 VDE 0660 VDE 0506 |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 5.0 cm |
| Package 1 Width | 7.5 cm |
| Package 1 Length | 200.0 cm |
| Package 1 Weight | 852.0 g |
| Unit Type of Package 2 | PAL |
| Number of Units in Package 2 | 512 |
| Package 2 Height | 115.0 cm |
| Package 2 Width | 200.5 cm |
| Package 2 Length | 120.0 cm |
| Package 2 Weight | 448.0 kg |
| Unit Type of Package 3 | CAR |

| | |
|------------------------------|----------|
| Number of Units in Package 3 | 8 |
| Package 3 Height | 10.5 cm |
| Package 3 Width | 14.0 cm |
| Package 3 Length | 200.5 cm |
| Package 3 Weight | 7.0 kg |

Offer Sustainability

| | |
|----------------------------|------------------------------------------------------------------------------------------------|
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|