


Product data sheet

Characteristics

AK2GD7575

Spacial CRN, Cable duct, 75 x 75 mm, without cover, grey



Main

Product or component type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	Spacial (S3D) Spacial (CRN) Thalassa PLA Thalassa PLS Thalassa PLM
Device composition	Without cover
Quantity per set	Set of 8

Complementary

Colour	Grey (RAL 7030)
Fixing mode	By screws Clip-on support
Material	PVC (polyvinyl chloride)
Height	75 mm
Length	2000 mm
Width	75 mm
Net weight	1.04 kg
Total number of wires	400

Environment

Ambient air temperature for operation	-5...60 °C
Flame retardance	V-0 conforming to UL 94
Fire resistance	960 °C conforming to IEC 60695-2-1/1
Standards	VDE 0506 DIN 43659 VDE 0660

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	7.5 cm
Package 1 Length	200.0 cm
Package 1 Weight	1.072 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	320
Package 2 Height	108.0 cm
Package 2 Width	201.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	377.0 kg
Unit Type of Package 3	CAR

Number of Units in Package 3	8
Package 3 Height	14.5 cm
Package 3 Width	15.5 cm
Package 3 Length	201.0 cm
Package 3 Weight	9.0 kg

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------