

## Product data sheet

### Characteristics

# AK2GD7575

Cable duct, Spacial CRN, 75 x 75 mm, without cover, grey

### Main

Product or component type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	PanelSeT S3D PanelSeT CRN Thalassa PLA Thalassa PLS Thalassa PLM
Device composition	Without cover
Quantity per set	Set of 8

### Complementary

Colour	Grey (RAL 7030)
Fixing mode	By screws Clip-on support
Material	PVC (polyvinyl chloride)
Height	75 mm
Length	2000 mm
Width	75 mm
Net weight	1.04 kg
Total number of wires	400

### Environment

Ambient air temperature for operation	-5...60 °C
Flame retardance	V-0 conforming to UL 94
Fire resistance	960 °C conforming to IEC 60695-2-1/1
Standards	VDE 0506 DIN 43659 VDE 0660

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.500 cm
Package 1 Width	7.500 cm
Package 1 Length	200.000 cm
Package 1 Weight	1.072 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	14.500 cm
Package 2 Width	15.500 cm
Package 2 Length	201.000 cm
Package 2 Weight	9.000 kg
Unit Type of Package 3	PAL

Number of Units in Package 3	320
Package 3 Height	108.000 cm
Package 3 Width	201.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	377.000 kg

### Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Take-back	No

### Contractual warranty

Warranty	18 months
----------	-----------