


## Product data sheet

### Characteristics

# AK2GD7575

Spacial CRN, Cable duct, 75 x 75 mm, without cover, grey



### Main

Product or component type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	Spacial S3D Spacial CRN Thalassa PLA Thalassa PLS Thalassa PLM
Device composition	Without cover
Quantity per set	Set of 8

### Complementary

Colour	Grey (RAL 7030)
Fixing mode	By screws Clip-on support
Material	PVC (polyvinyl chloride)
Height	75 mm
Length	2000 mm
Width	75 mm
Net weight	1.04 kg
Total number of wires	400

### Environment

Ambient air temperature for operation	-5...60 °C
Flame retardance	V-0 conforming to UL 94
Fire resistance	960 °C conforming to IEC 60695-2-1/1
Standards	VDE 0506 DIN 43659 VDE 0660

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	7.5 cm
Package 1 Length	200.0 cm
Package 1 Weight	1.072 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	320
Package 2 Height	108.0 cm
Package 2 Width	201.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	377.0 kg
Unit Type of Package 3	CAR

Number of Units in Package 3	8
Package 3 Height	14.5 cm
Package 3 Width	15.5 cm
Package 3 Length	201.0 cm
Package 3 Weight	9.0 kg

## Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------