

Product data sheet

Characteristics

AP9631

UPS Network Management Cards, UPS Network Management Card 2 with Environmental Monitoring



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Provided equipment	CD with software Temperature sensor User manual
--------------------	---

Physical

Colour	Black
Height	3.8 cm
Width	12.1 cm
Depth	11.4 cm
Net weight	0.09 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable

Conformance

Standards	EN 55022 class A EN 55024 FCC part 15 class A ICES-003
Product certifications	AS/NZS 3548 (C-Tick) class A GOST VCCI class A

Environmental

Ambient air temperature for operation	0...45 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 %
Ambient air temperature for storage	-5...45 °C
Storage altitude	0.00...15240.00 m
Storage Relative Humidity	0...95 %

Communications & Management

Authentication	Radius
----------------	--------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.1 cm
Package 1 Width	23.5 cm
Package 1 Length	15.9 cm
Package 1 Weight	0.339 kg
Unit Type of Package 2	S03
Number of Units in Package 2	4
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	2.32 kg
Unit Type of Package 3	PAM
Number of Units in Package 3	600
Package 3 Height	138.2 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	301.92 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
Mercury free	Yes
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------