

Product data sheet

Characteristics

B15/15A-WE

Switched Socket, Metal Plate Series, Single B Style Stainless Steel

Main

Range of product	Metal Plate
Product or component type	Switched socket
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number Of Outlets	1
Actuator	Rocker Switch
Mounting Type	By screws
Local signalling	Without light indicator
Installation Orientation	Horizontal
Material	Stainless steel
[Ue] rated operational voltage	250 V AC
[In] rated current	15 A
Depth	30 mm
Length	115 mm
Width	70 mm
Mounting Centers	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	7 cm
Package 1 Length	11.5 cm
Package 1 Weight	0.16 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	117 cm

Package 2 Width	148 cm
Package 2 Length	167 cm
Package 2 Weight	1.6 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	254 cm
Package 3 Width	348 cm
Package 3 Length	445 cm
Package 3 Weight	16 kg

Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations