

Product data sheet

Characteristics

B15/15A-WE

Single Switched Socket B Style Stainless Steel



Main

Range of product	Metal Plate
Product or component type	Switched socket
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Rocker Switch
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Stainless steel
[Ue] rated operational voltage	250 V AC
[In] rated current	15 A
Depth	30 mm
Length	115 mm
Width	70 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	7 cm
Package 1 Length	11.5 cm
Package 1 Weight	0.16 kg
Unit Type of Package 2	Gyári csomagolás
Number of Units in Package 2	10
Package 2 Height	117 cm
Package 2 Width	148 cm

Package 2 Length	167 cm
Package 2 Weight	1.6 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	254 cm
Package 3 Width	348 cm
Package 3 Length	445 cm
Package 3 Weight	16 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile