

Product data sheet

Characteristics

B15M-WE

Single Switch Socket Outlet Mechanism, 250V, 10A, B Style, Flat Plate



Main

Range of product	Metal Plate
Product or component type	Switched socket
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Rocker Switch
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Stainless steel
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Length	96 mm
Width	55 mm
Fixing center	64 mm

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Weight	0.075 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile