

## Product data sheet

### Characteristics

# B15VM-WE

## SWITCH MECH ONLY B STYLE S/S



### Main

Range of product	Metal Plate
Product or component type	Switched socket
Product brand	Clipsal
Colour	White electric

### Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Rocker Switch
Mounting position	Vertical
Fixing mode	By screws
Local signalling	Without light indicator
Material	Stainless steel
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	32.5 mm
Length	95 mm
Width	55 mm
Fixing center	84 mm

### Packing Units

Package 1 Weight	0.001 kg
Package 1 Height	32.000 mm
Package 1 width	55.000 mm
Package 1 Length	95.000 mm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>