

## Product data sheet

### Characteristics

# B15VM-WE

## Metal Plate Series, Single Switch Socket Outlet Mechanism, 250V, 10A, B Style, Flat Plate, Vertical

### Main

Range of product	Metal Plate
Product or component type	Switched socket
Product brand	Clipsal

### Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number Of Outlets	1
Actuator	Rocker Switch
Mounting Type	By screws
Local signalling	Without light indicator
Installation Orientation	Vertical
Material	Stainless steel
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	32.5 mm
Length	95 mm
Width	55 mm
Mounting Centers	84 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.2 cm
Package 1 Width	5.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	68 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	11.7 cm
Package 2 Width	14.3 cm
Package 2 Length	18.1 cm
Package 2 Weight	680 g
Unit Type of Package 3	CAR

Number of Units in Package 3	100
Package 3 Height	25.4 cm
Package 3 Width	34.8 cm
Package 3 Length	44.5 cm
Package 3 Weight	6800 g

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations