

Product data sheet

Characteristics

BA15VA-BK

SOCKET SWITCHED SINGLE A STYLE BRASS



Main

Range of product	Metal Plate
Product or component type	Switched socket
Product brand	Clipsal
Colour	Black

Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Switch Rocker
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Vertical
Material	Brass
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	35 mm
Length	115 mm
Width	70 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	160.0 g
Package 1 Height	3.5 cm
Package 1 width	7 cm
Package 1 Length	11.5 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	25
Package 2 Weight	4000.0 g

Package 2 Height	11.7 cm
Package 2 width	25 cm
Package 2 Length	31 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	5
Package 3 Weight	800.0 g
Package 3 Height	11.7 cm
Package 3 width	10.2 cm
Package 3 Length	13.8 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information