

Product data sheet

Characteristics

BA25A-WE

Metal Plate Series, Twin Switch Socket Outlet, 250V, 10A, A Style, Deep Curve Plate



Main

Range of product	Metal Plate
Product or component type	Switched socket
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number Of Outlets	2
Actuator	Switch Rocker
Mounting Type	By screws
Local signalling	Without light indicator
Installation Orientation	Horizontal
Material	Brass
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	28 mm
Length	130 mm
Width	86 mm
Mounting Centers	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	8.6 cm
Package 1 Length	13 cm
Package 1 Weight	0.2 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	117 cm

Package 2 Width	102 cm
Package 2 Length	138 cm
Package 2 Weight	1 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	157 cm
Package 3 Width	305 cm
Package 3 Length	445 cm
Package 3 Weight	10 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations