

## Product data sheet

### Characteristics

# BA25A-WE

## SWITCHED SOCKET TWIN A STYLE BRASS



### Main

Product or component type	Switched socket
Colour	White electric
Product brand	Clipsal
Range of product	Metal Plate

### Complementary

Colour code	WE
Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Switch Rocker
Mounting position	Horizontal
Fixing mode	By screws
Local signalling	Without light indicator
Material	Brass
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	28 mm
Length	130 mm
Width	86 mm
Fixing center	84 mm

### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.2 kg
Package 1 Height	28 mm
Package 1 width	86 mm
Package 1 Length	130 mm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>