

Product data sheet

Characteristics

BA25X-WE

SWITCHED SOCKET TWIN A STYLE BRASS



Main

Range of product	Metal Plate
Product or component type	Switched socket
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Switch Rocker
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Brass
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	28 mm
Length	130 mm
Width	86 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	8.6 cm
Package 1 Length	13.0 cm
Package 1 Weight	0.225 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile