

Product data sheet

Characteristics

BA25X-WE

SWITCHED SOCKET TWIN A STYLE BRASS



Main

Product or component type	Switched socket
Colour	White electric
Product brand	Clipsal
Range of product	Metal Plate

Complementary

Colour code	WE
Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Switch Rocker
Mounting position	Horizontal
Fixing mode	By screws
Local signalling	Without light indicator
Material	Brass
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	28 mm
Length	130 mm
Width	86 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.225 kg
Package 1 Height	28 mm
Package 1 width	86 mm
Package 1 Length	130 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile