

## Product data sheet

### Characteristics

# BA31VA-WE

Flush Switch 1 Gang, Metal Plate Series,  
250VAC, 10A, A Style, Standard, Vertical



#### Main

Range of product	Metal Plate
Product brand	Clipsal
Assembly Type	Basic element with full cover plate and grid

#### Complementary

Installation Type	Flush
Number Of Switches	1
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking
Mounting Type	By screws
Actuator	Rocker
Switch function	1-way 2-way

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	7 cm
Package 1 Length	11.5 cm
Package 1 Weight	129 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	117 cm
Package 2 Width	102 cm
Package 2 Length	138 cm
Package 2 Weight	0.7 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	254 cm
Package 3 Width	348 cm
Package 3 Length	445 cm
Package 3 Weight	14 kg

## Offer Sustainability

---

EU RoHS Directive

Compliant with Exemptions

---

China RoHS Regulation

 [China RoHS Declaration](#)

---