

Product data sheet

Characteristics

BB15V2A-BK

SWITCHED SOCKET TWIN B STYLE BRASS



Main

Product or component type	Switched socket
Colour	Black
Product brand	Clipsal
Range of product	Metal Plate

Complementary

Colour code	BK
Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Switch Rocker
Mounting position	Vertical
Fixing mode	By screws
Local signalling	Without light indicator
Material	Brass
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	35 mm
Length	115 mm
Width	115 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.35 kg
Package 1 Height	35 mm
Package 1 width	115 mm
Package 1 Length	115 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile