

Product data sheet

Characteristics

BB15VA-BK

SOCKET SWT SING B STYLE BS



Main

| | |
|---------------------------|-----------------|
| Range of product | Metal Plate |
| Product or component type | Switched socket |
| Product brand | Clipsal |
| Colour | Black |

Complementary

| | |
|--------------------------------|-------------------------|
| Control type | ON/OFF button |
| Number of gangs | 1 gang |
| Pin number | 3 |
| Number of power socket outlets | 1 |
| Actuator | Rocker Switch |
| Fixing mode | By screws |
| Local signalling | Without light indicator |
| Mounting position | Vertical |
| Material | Brass |
| [Ue] rated operational voltage | 250 V AC |
| [In] rated current | 10 A |
| Depth | 35 mm |
| Length | 115 mm |
| Width | 70 mm |
| Fixing center | 84 mm |

Environment

| | |
|-----------|---|
| Standards | AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1 |
|-----------|---|

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3.5 cm |
| Package 1 Width | 7 cm |
| Package 1 Length | 11.5 cm |
| Package 1 Weight | 0.2 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |