

Product data sheet

Characteristics

BB25X-BK

Metal Plate Series, Switched Socket Twin B Style Brass

Main

Range of product	Metal Plate
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Switch Rocker
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Brass
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	35 mm
Length	130 mm
Width	86 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	8.6 cm
Package 1 Length	13.0 cm
Package 1 Weight	225.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	20
Package 2 Height	25.0 cm

Package 2 Width	21.4 cm
Package 2 Length	33.8 cm
Package 2 Weight	20.0 kg