

Product data sheet

Characteristics

BB5032NL-WE

KEY INPUT C-BUS 2 GANG LEARN



Main

Range of product	Metal Plate Multi-Gang Series C-Bus
Product brand	Clipsal
Colour	White electric

Complementary

Number of gangs	2 gangs
Product destination	Switch
Fixing mode	By screws
Material	Brass
Control type	Button
Marking	Without marking
Mounting position	Vertical
Fixing center	84 mm
Thickness	19 mm
Length	116 mm
Width	76 mm
Colour code	WE

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	180 g
Package 1 Height	1.9 cm
Package 1 width	7.6 cm
Package 1 Length	11.6 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	25
Package 2 Weight	4.7 kg
Package 2 Height	23.5 cm
Package 2 width	25.1 cm
Package 2 Length	29.6 cm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information