

Product data sheet

Characteristics

BP165C6

Clipsal MAX4, Link bar 165 A 6 hole length 95 mm 1 hexagon head



Main

Product brand	Clipsal
Range of product	Series BP165C Blue Point
Product or component type	Link bar

Complementary

Cable cross section	16 mm ²
[In] rated current	165 A
Connector type	Screw terminals
Number of poles	1
Height	95 mm
Width	19 mm
Depth	9.5 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2 cm
Package 1 Width	1.9 cm
Package 1 Length	7.2 cm
Package 1 Weight	100 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Circularity Profile	No need of specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.