

Product data sheet

Characteristics

BP2

Max 4 Link Bars, Strip Connectors, 20A, 12 Terminal, Double Entry Bakelite



Main

Product brand	Clipsal
Range of product	Blue Point

Complementary

Cable cross section	4 mm ² fine stranded without cable end sleeve
[In] rated current	20 A
Connector type	1 screw terminals 2 screw terminals
Number of poles	12
Mounting support	Panel
Material	Bakelite: insulation
Width	17 mm grid pattern:
Minimum mounting height	16 mm
Length	122 mm

Environment

Ambient air temperature for operation	190 °C
---------------------------------------	--------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	1.8 cm
Package 1 Length	12.1 cm
Package 1 Weight	48.4 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information

 [Yes](#)

Environmental Disclosure

 [Product Environmental Profile](#)
