

Product data sheet

Characteristics

BP3

CONNECTOR STRIP 12TERM 20A



Main

Product brand	Clipsal
Range of product	Blue Point

Complementary

Distance between centers	Hole: 23 mm
Cable cross section	4 mm ² fine stranded without cable end sleeve
[In] rated current	20 A
Connector type	1 screw terminals 2 screw terminals
Number of poles	12
Mounting support	Panel
Material	Bakelite: insulation
Width	17 mm grid pattern:
Minimum mounting height	16 mm
Length	139 mm

Environment

Ambient air temperature for operation	190 °C
---------------------------------------	--------

Packing Units

Package 1 Weight	0.065 kg
------------------	----------

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration