

## Product data sheet

### Characteristics

# BP504F10

## Blue Point Fused Terminal Blocks, 250V, 3 Terminal, 10A, Fuse



### Main

Product brand	Clipsal
Range of product	Blue Point
Product destination	Fuse holder by screws
Colour	White

### Complementary

Fuse type	Cartridge
Cable cross section	6 mm <sup>2</sup> , fine stranded cable without cable end sleeve
[In] rated current	10 A
Fixing mode	By screws
Width	18 mm grid pattern:
Minimum mounting height	33 mm
Length	42 mm

### Environment

Ambient air temperature for operation	120 °C
---------------------------------------	--------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	20 cm
Package 1 Width	33 cm
Package 1 Length	44 cm
Package 1 Weight	0.019 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	55 cm
Package 2 Width	80 cm
Package 2 Length	120 cm
Package 2 Weight	0.38 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	500
Package 3 Height	250 cm
Package 3 Width	214 cm
Package 3 Length	338 cm
Package 3 Weight	9.5 kg

## Offer Sustainability

EU RoHS Directive

Under investigation

Environmental Disclosure

 [Product Environmental Profile](#)